

# Datasheet

## Spirit Level

# Starrett®

RS Stock number [724-3778](#)



### Description:

This level has ground and graduated main vials and a cross test vial. The Cast Iron base of the level features an involute groove running the length of the base, which provides a reliable seat for round work such as pipes or shafting. With the cross test vial, it is possible to simultaneously level in both directions. This prevents inaccuracies in the main vial reading caused by canting the level sidewise on round work.

The 150-450mm main level vials have graduations that are approximately 0.42mm per meter or 80-90 seconds. There are five, six, or seven lines on each side of the bubble, depending on the base length. A bubble movement of 2.5mm (1 graduation) indicates a tilt from the horizontal of 0.12mm per 300mm.

### Features:

Frame Material:	Cast Iron
Length:	154 mm
Model Number:	DW886