


DRAWING MADE IN AMERICAN PROJECTION

G 100

© 1957 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS

CTR	DESCRIPTION	DATE	APPROVED
C	RE-DRAWN REV ADDED TAPE NO. B-630	4-1-70	FCY
D	REV/6726-0066-93	4-8-93	TG/ml



FOR .105 TO .150 WIRE INSULATION DIA.
TONGUE MATERIAL THK = .031^{±.002}

100	LOOSE PC BOX	8-324159-1		
1	324159 ON TAPE	2-324159-2	BODY & SLEEVE: COPPER (QQ-C-576) TIN PL (MIL-T-10727)	
1	WIRE TERMINAL	324159	INSULATION: NYLON (MIL-M-20693) TYPE I COLOR: BLUE	
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS: ±.008 ANGLES: ±.5°		CONTRACT NO. DR. <i>St. L.</i> 3-20-70 CHK <i>EC</i> 4-1-70 APPD <i>Wabel</i> 4-2-70 REL <i>FCY</i> 4-2-70 OSGN APPD OTHER APPD	 AMP INCORPORATED HARRISBURG, PENNSYLVANIA NAME: WIRE TERMINAL P.I.D.G.-RING TONGUE WIRE SIZE: 16-14 SIZE: A CODE IDENT NO.: 00779 NUMBER: 324159 SCALE: NTS SHEET: 1 OF 1	
MATERIAL SEE TABLE				