

Protective covers - HC-B 16-TMS-SD-IP65 - 1690794


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON ADVANCE IP65 protective cover B16, for panel mounting side, with screw locking, with retaining cord, diameter of retaining cord eyelet 3 mm



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 890681
Weight per Piece (excluding packing)	54.2 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Diameter of retaining cord eyelet	3.5 mm
-----------------------------------	--------

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 100 °C

General

Type	B16
	HC-ADVANCE protective cover
Seal material	NBR
Locking latch material	High-grade steel
Inflammability class according to UL 94	V0
Color	gray
Seal present	Yes
Assembly instructions	Tightening torque of locking screw: 3 Nm

Protective covers - HC-B 16-TMS-SD-IP65 - 1690794

Classifications

eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27142104
eCl@ss 5.1	27142104
eCl@ss 6.0	27142104
eCl@ss 7.0	27142104

ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002040
ETIM 5.0	EC002040

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

Protective covers - HC-B 16-TMS-SD-IP65 - 1690794

Dimensioned drawing

