

Cable - CABLE-50/4FLK14/ 6,0M/YUC - 2318978

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Assembled round cable with a 50-pos. molded socket strip and four 14-pos. socket strips, for splitting 32 channels into 4x8 channels, number of positions: 50/4x14; the cable is suitable for the ADV551 and ADV151 boards. Cable length: 6.0 m

Why buy this product

- Four 14-pos. connectors on the module side for connecting four 8-channel VARIOFACE modules of the system cabling
- Lateral cable outlet of the I/O module



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 326070 |
| Weight per Piece (excluding packing) | 400.0 g |
| Custom tariff number | 85444290 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

General

| | |
|---|---|
| Nominal voltage U_N | 30 V DC |
| Max. current carrying capacity per path | 500 mA (Up to 55°C ambient temperature) |
| Max. conductor resistance | 0.16 Ω /m |
| Length of cable | 6 m |
| Single wire, cross section | 0.14 mm ² |
| AWG | 26 |
| Conductor construction: Number of litz wires: | 7 |
| External diameter | 11 mm |
| Shielding | no |
| Outer sheath, material | PVC |
| External sheath, color | Gray RAL 7035 |

Environmental conditions

Cable - CABLE-50/4FLK14/ 6,0M/YUC - 2318978

Technical data

Environmental conditions

| | |
|---|------------------------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Flame resistance | IEC 60332-1 |
| Resistance to oil | DIN VDE 0472 Part 803, test type B |
| Gasoline resistance | Against occasional splashes |

Connector, module side

| | |
|---------------------|--------------------------------|
| Number of positions | 14 |
| Connectors | IDC/FLK socket strip (2.54 mm) |
| Number of plugs | 4 |

Connector, controller side

| | |
|---------------------|--------------------------------|
| Number of positions | 50 |
| Connectors | IDC/FLK socket strip (2.54 mm) |
| Number of plugs | 1 |

Connection data

| | |
|-------------------|------------------|
| Connection method | Screw connection |
| Torque | 0.5 Nm |

Supported controller

| | |
|---------------------|--------------------------|
| Controller | YOKOGAWA CENTUM CS3000R3 |
| - suitable I/O card | ADV151 |
| | ADV551 |
| Controller | YOKOGAWA STARDOM |
| - suitable I/O card | NFDV151 |
| | NFDV551 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27249205 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |

Cable - CABLE-50/4FLK14/ 6,0M/YUC - 2318978

Classifications

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC000237 |
|----------|----------|

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11 | 26121620 |
| UNSPSC 12.01 | 26121620 |
| UNSPSC 13.2 | 26121620 |

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

| |
|-----|
| EAC |
|-----|

Drawings

Cable - CABLE-50/4FLK14/ 6,0M/YUC - 2318978

Connection diagram

| 50-pos. connector to the I/O card | 4 x 14-pos. connector to the module | Wire color |
|---|---|---------------|
| 50 | 1 | black |
| 49 | 3 | brown |
| 48 | 5 | red |
| 47 | 7 | orange |
| 46 | 9 | yellow |
| 45 | 11 | green |
| 44 | 13 | blue |
| 43 | 15 | violet |
| 42 | 44 | gray |
| 41 | 39 | white |
| 40 | 17 | white-black |
| 39 | 19 | white-brown |
| 38 | 21 | white-red |
| 37 | 23 | white-orange |
| 36 | 25 | white-yellow |
| 35 | 27 | white-green |
| 34 | 29 | white-blue |
| 33 | 31 | white-violet |
| 32 | 43 | white-gray |
| 31 | 37 | brown-black |
| 30 | 2 | brown-red |
| 29 | 4 | brown-orange |
| 28 | 6 | brown-yellow |
| 27 | 8 | brown-green |
| 26 | 10 | brown-blue |
| 25 | 12 | brown-violet |
| 24 | 14 | brown-gray |
| 23 | 16 | brown-white |
| 22 | 42 | green-black |
| 21 | 36 | green-brown |
| 20 | 18 | green-red |
| 19 | 20 | green-orange |
| 18 | 22 | green-blue |
| 17 | 24 | green-violet |
| 16 | 26 | green-gray |
| 15 | 28 | green-white |
| 14 | 30 | yellow-black |
| 13 | 32 | yellow-brown |
| 12 | 41 | yellow-red |
| 11 | 34 | yellow-orange |