

General Information

Extended Product Type:	BJS10-10
Product ID:	1SNA164588R2200
EAN:	3472591645880
Catalog Description:	BJS10-10 Jumper Bars
Long Description:	BJS10-10 - Jumper Bars - 10 poles - - 10mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472591645880
Minimum Order Quantity:	10 piece
Customs Tariff Number:	74199990

Dimensions

Product Net Weight:	8.5 g
---------------------	-------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Gross Weight:	0.085 kg
Package Level 1 EAN:	3472591645880
Package Level 2 Units:	1500 piece

Additional Information

Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Type:	Use of this accessory requires the user to cut out the partition.
Product Main Type:	BJS
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 57 A
Spacing:	10 mm
Sub-Function:	Not Assembled Jumper bar
Sub-Function 2:	Screw
Suitable For:	M10/10.RS

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Declaration of Conformity - CE:	1SND225001C1009

Classifications

ETIM 4.0:	EC000489 - Cross-connector for terminal block
ETIM 5.0:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

