


LOC	DIST	REVISEMENTS 変更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	-		B	REVISED FJ00-0588-01	03APR2001	C.O	K.I



1. 締付け最大トルク値; 8Kg-cm
2. 一般公差; 10mm以下 ± 0.2
10mm以上 ± 0.25
3. 材料; 炭素鋼
4. 仕上; ニッケルめっき

1. SCREW ON TORQUE MAX; 8Kg-cm
2. GENERAL TOLERANCE; 10mmMAX. ± 0.2
10mmMIN. ± 0.25
3. MATERIAL; CARBON STEEL
4. FINISH; NICKEL PL.

(B)	OBSOLETE	5.5	7.92	172617-6
		4.78	10.0	172617-5
		4.78	14.22	172617-2
		4.78	7.92	172617-1
	"B"	"A"	PARTS NUMBER	

DIMENSIONS: 単位: 概 mm		DWN C.OHASHI	03APR2001	MATERIAL 材料		3	FINISH 仕上		4				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 2		CHK K.IKEGAMI	03APR2001	AMP Tyco Electronics AMP K.K. Kawasaki, Japan					NAME 名称				
		APVD K.IKEGAMI	03APR2001										
		PRODUCT SPEC 製品規格		SCREWLOCK FEMALE FOR AMPLIMITE									
		APPLICATION SPEC 取付適用規格											
0 PLC $\pm$		WEIGHT		SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO						
1 PLC ± 0.1				A 4	00779	C-172617							
2 PLC ± 0.01													
3 PLC ± 0.001													
4 PLC ± 0.0001													
ANGLES $\pm$													
CUSTOMER DRAWING				SCALE 尺度	4:1	SHEET 張	1	OF OF	1				
						REV	B						