

# Pilot devices – Modular range

## Pilot light, buzzer and potentiometer



Description/Supply voltage	Type	Order Code	Weight, kg
<b>Pilot light head</b>	<b>ML1-100■</b>	<b>1SFA 611 400 R100■</b>	0.018
<b>Lamp block with holder:</b> For max. 2 W, 230 V AC and DC filament bulb or LED	<b>MCBH-001</b>	<b>1SFA 611 605 R1200</b>	0.021
115 V AC supply voltage. For 60 V filament bulb max. 1.2 W	<b>MCBH-002</b>	<b>1SFA 611 605 R1300</b>	0.023
230 V AC supply voltage. For 130 V filament bulb max. 2 W	<b>MCBH-003</b>	<b>1SFA 611 605 R1400</b>	0.026
For a softer light output and 180 degrees smooth light distribution use text cap with or without text..			
<b>Text cap without text</b>	-	<b>1SFA 616 903 R9001</b>	
For increased visibility from far distance use a light diffusing lens.			
<b>Light diffusing lens</b>	<b>KA1-8005</b>	<b>1SFA 616 920 R8005</b>	0.001
Description/Supply voltage	Type	Order Code	Weight, kg
<b>Buzzer</b> Frequency: 2400 Hz Rated current: ≤8 mA Loudness: Min. 80 dB(A)/10 cm <i>Continuous tone type:</i>			
24 V AC/DC	<b>KB1-4010</b>	<b>1SFA 616 401 R4010</b>	0.020
115V AC/DC	<b>KB1-4030</b>	<b>1SFA 616 401 R4030</b>	0.020
230 V AC/DC	<b>KB1-4040</b>	<b>1SFA 616 401 R4040</b>	0.020
<i>Pulsating tone type:</i>			
24 V AC/DC	<b>KB1-4110</b>	<b>1SFA 616 401 R4110</b>	0.020
115V AC/DC	<b>KB1-4130</b>	<b>1SFA 616 401 R4130</b>	0.020
230 V AC/DC	<b>KB1-4140</b>	<b>1SFA 616 401 R4140</b>	0.020
<b>Potentiometer/Resistor</b> Black knob with integrated position indication and marking in white			
5 kohm	<b>KT-105B</b>	<b>1SFA 616 410 R1056</b>	0.034
10 kohm	<b>KT-110B</b>	<b>1SFA 616 410 R1106</b>	0.034
<b>Operating knob - without resistor</b> Black knob with integrated position indication and marking in white. For shaft diameter 6 - 6.35 mm. Min. shaft length 20 mm	<b>KT-100B</b>	<b>1SFA 616 410 R1006</b>	0.023

### Color codes for pilot light head

Type	Order Code
■ □	□
Red <b>R</b> ●	1
Green <b>G</b> ●	2
Yellow <b>Y</b> ●	3
Blue <b>L</b> ●	4
White <b>W</b> ○	5
Clear <b>U</b> ○	8

### Ordering example

Requested: A red pilot light with a red LED.  
Supply voltage 115 V AC  
Order 1 piece of each:  
ML1-100R  
MCBH-001  
KA2-2131 (= LED acc. to page 18)

