

BJA6-10

ABB contact for United
States of America



General Information

Extended Product Type:	BJA6-10
Product ID:	1SNA116541R1200
EAN:	3472591165418
Catalog Description:	BJA6 Jumper Bars
Long Description:	BJA6-10 - Jumper Bars - 10 poles - - 6mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472591165418
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	12.00 g
----------------------------	---------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	155 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0.12000 kg
Package Level 1 EAN:	3472591165418
Package Level 2 Units:	1000 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 3 Units:	48000 piece

Additional Information

Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Type:	This accessory permits the interconnection of consecutive or non-consecutive blocks. For this, detach the studs manually where connection is not required. The use of two bars permits alternated jumping. A captive screw is mounted on each stud. This jumper
Product Main Type:	BJA
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 35 A
Spacing:	6 mm
Sub-Function 2:	Screw

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225001C1009
GOST Certificate: 1SND161005A1104

Classifications

E-nummer: 2925727
ETIM 4.0: EC000489 - Cross-connector for terminal block
ETIM 5.0: EC000489 - Cross-connector for terminal block
Object Classification Code: X

