

ITT 1000 W 235 V-01X0

HALOTHERM | Infrared halogen lamps, quartz clear



Areas of application

- Plastics, paper and printing industries
- Drying paint and varnishes
- Coil coating
- Keeping food warm in restaurants

Product benefits

- Short response time
- High efficiency
- Precise controllability
- Long lamp life



Product datasheet

Technical data


Electrical data

Nominal wattage	1000.00 W
Nominal voltage	235 V
Nominal current	4.3 A
Lamp current	4.30000 A
Construction voltage	235 V

Photometrical data

Color temperature	2350 K
-------------------	--------

Dimensions & weight



Length	365.0 mm
Filament length	270.00 mm

Lifespan

Lifespan	5000 h
----------	--------

Additional product data

Base (standard designation)	X ¹⁾
-----------------------------	-----------------

¹⁾ Metal strip connection according to EN 60240-1

Capabilities

Burning position	p15
------------------	-----

Country specific information

Product code	METEL-Code	SEG-No.	STK number	UK Org
4008321555076	-	-	4739773	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321555076	ITT 1000 W 235 V- 01X0	Role 1	44 mm x 44 mm x 645 mm	1.25 dm ³	181.00 g
4008321555083	ITT 1000 W 235 V- 01X0	Shipping carton box 12	190 mm x 150 mm x 660 mm	18.81 dm ³	2420.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.