F-1400 | DUAL POWER ALUMINIUM FLASHLIGHT

- High quality 1400 lumen white LED, 6500k
- Hard anodized die cast matte aluminium body
- Tactical rubberised tail switch
- 4 light modes and 8Hz defence strobe
- Flawless smooth reflector for long distance beam
- IP68 dust and waterproof - 1m submersible
- Impact resistant to 2m
- Built-in concealed USB-C charging port
- Battery level and charging indicator LED

- Circuit Protection prevents battery from over-charging or over-discharging
- Fast 1A USB-C charging - 2.5 hour charge time
- High quality USB-C charging cable inc. (0.5m)
- Can also work with 2 x CR123A lithium batteries (not inc.)
- Safety nylon wrist strap included

BATTERY 3.6v 2600mAh 18650 Li-ion (inc.) / or 2 x CR123A batteries (not inc.)
WEIGHT 157g (with li-ion battery) / 109g (without battery)
DIMENSIONS 140 x Ø 30x Ø 25mm

LUMEN 1400LM | **RUNTIME** 2.5-23H | **BEAM** 180M | **IP RATING** IP68