






Matchcode	Description	Picture	Technical data	Colours
VSFK 6000 / 2,5 / ..(length) / ..(colour) length: 25cm 50cm 100cm 150cm 200cm	<b>Measuring lead</b> <ul style="list-style-type: none"> <li>2 safety lamella-basket plugs crimped on highlyflexible double insulated PVC-lead 2,5 mm<sup>2</sup></li> <li>contact parts nickel-plated</li> </ul>		lead: PVC-isol. 2,5 mm <sup>2</sup> transition resistance as a function to length: 5 mΩ, 9 mΩ, 17 mΩ, 25 mΩ, 35 mΩ rated voltage: 1000 V CAT III rated current: 32 A operating temperature: -10 °C ... +80 °C	black, red blue, yellow green, grey, brown, white, purple, green-yellow
VSFK 6001 / 2,5 / ..(length) / ..(colour) length: 25cm 50cm 100cm 150cm 200cm	<b>Measuring lead</b> <ul style="list-style-type: none"> <li>2 safety lamella-basket plugs crimped on highlyflexible double insulated PVC-lead 2,5 mm<sup>2</sup></li> <li>contact parts gold-plated</li> </ul>		lead: PVC-isol. 2,5 mm <sup>2</sup> transition resistance as a function to length: 5 mΩ, 8 mΩ, 14 mΩ, 22 mΩ, 27 mΩ rated voltage: 1000 V CAT III rated current: 32 A operating temperature: -10 °C ... +80 °C	black, red blue, yellow green, grey, brown, white, purple, green-yellow
SWEB 6656 Au / ..(colour)	<b>Angled safety socket</b> <ul style="list-style-type: none"> <li>angled safety socket for PCB</li> <li>socket Ø 4 mm</li> </ul>		terminal: PCB transition resistance: 10 mΩ rated voltage: 1000 V CAT III rated current: 24 A operating temperature: -25 °C ... +80 °C	black, red
SAB 6922 Ni / ..(colour) SAB 6922 Au / ..(colour)	<b>Safety threaded socket</b> <ul style="list-style-type: none"> <li>for fitting into panels up to 6 mm thick</li> <li>fastening: slotted nut M12 x 0,75 and spring washer</li> </ul>		terminal: M4 transition resistance: 5 mΩ (Ni) / 3 mΩ (Au) rated voltage: 1000 V CAT III rated current: 32 A operating temperature: -25 °C ... +80 °C max. torque for the fastening nuts: 45 Ncm	black, red blue, yellow green, grey, brown white, purple
SKURZ 6760 / 19-4 IG 2MB Ni / ..(colour)	<b>Connecting plug</b> <ul style="list-style-type: none"> <li>moulded insulation</li> <li>with rear sockets Ø 4 mm</li> </ul>		terminal: rear socket 4 mm (2x) transition resistance: 8 mΩ rated voltage: 1000 V CAT II rated current: 32 A operating temperature: -15 °C ... +70 °C	black, red blue, green, grey, brown, green-yellow