

## Metal tool box with assortment, 134 pieces 1/4 " + 3/8", inch sizes, 1483KHD3RB-FF5



Article number: 1483KHD3RB-FF5

Size: 523x257x300cm

Weight: 11,000 g

Packing quantity: 1pc. "

134-piece Metal tool case, range 1/4 " + 3/8" inch sizes

- For aircraft mechanics
- Suitable for all major aircraft types
- Especially suitable for maintenance 1/4 ", 3/8"

### Lid Compartment



481-500  
Hammer

500g

3625N-32  
Superflex plastic hammer

300g

2509  
Flexible gripper

525 mm

7762  
Extension 3/8 "

250mm

## 78-Piece



Combination spanner angled	111Z	1", 1.1 / 8"
Double open ended spanner set	6Z / 8C	1/ 4x5/16", 5/16x11/32", 3/8x7/16" 1/2x9/16", 19/32x11/16", 5/ 8x3/4", 13/16x7/8", 15/16x1"
Open-ended spanner	6Z	1x1.1 / 8", 1.1/16x1.1/4" / td>
Ratchet 1/4 "Narrow head	6950SL	-
Renewals 1/4 "	6960/6961	50, 100 mm
Flexible handle 1/4 "	6958	-
Universal joint 1/4 "	6966	-
Ratchet 3/8 "Narrow head	7750SL	-
Crank 3/8 "	7752	-
Universal joint 3/8 "	7766	-
Renewals 3/8 "	7760/7761	75, 125 mm
3/8 "to 1/4" transitional part	7764	-
1/4 "to 3/8" transitional part	7765	-
3/8 "to 1/2" transitional part	8164-1 / 2	-
1/2 "to 3/8" transitional part	8165-1 / 2	-
Bit holder 1/4 "	6972H	-
Bit holder 3/8 "	7407H	1/4 "- 3/8"
Bit holder 3/8 "	7408H	5/16 "- 3/8"
Sockets 1/4 ", double short	A6700DZ	7/32", 1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16"
Sockets 1/4 ", double long	A6800DZ	7/32", 1/4", 9/32", 5/16"
Sockets 3/8 ", double short	A7400DM	10, 13 mm
Sockets 3/8 ", double	A7402DZ	3/8", 7/16", 1/2", 9/16"
Steckschl.Einsätze 1/4 ", double, ZOLL	7800DZ	15/16", 1" 59 / S28-4
Bit set TORQ-SET® Screws 28-Piece	59 / S28-4	-

## Foam insert Screwdriver, 14-piece



Flexible scale, stainless	1179-FLX-2	300 mm
Double angled offset screwdriver for slotted screws	2047-1.2-8	0,8x4x100
Double angled offset screwdriver for Phillips screws	2047PR-1-2	PH1, 2
Ergo screwdriver for slotted screws	BE-8020L	0,5x3x75
Ergo screwdriver for slotted screws	BE-8155	1,2x6,5x125
Ergo screwdriver for slotted screws, hex shaft and approach	BE-8260	1,6x8,0x175
M. screwdriver through-blade for slotted screws	9715-14-250	2.5x14x250
Ergo screwdriver	BE 8601/	
for Phillip screws, short version	BE 8602	PH1x25, PH2x25
Ergo screwdriver for Phillip screws	BE-8611/	
	BE 8621	PH1x75, PH2x100
Scriber cranked,	1177-SCRIBE	230 mm
Telescopic articulated mirror	5515T-52	Ø 50 mm
O-ring Lever	BE-3529	175 mm

## 12-piece



Ergo side cutter	2101 GC-160IP	160mm
Needle nose pliers	2427 GC-200 IP	200mm
Wire twisting pliers	2855D	282mm
Ergo Water Pump Pliers	8224CIP	-
Tape measure	MTB-3-16-E	3m
Driver M. Hand Protection	3658A	3x150, 5x150, 8x150mm
ALU-buckthorn	454800500	25x150mm
2-cell flashlight	BFLB01	-
Flat chisel	3740-150	150mm
Grains	3735-4-120	120mm

## 27-piece



Open-ended spanner, cranked, customs	1300Z	1 / 4x5 / 16 " , 3 / 8x7 / 16 "
Open-ended spanner, Liliput	1931Z	7/32 " , 1/4 "
Open-ended spanner	DS2018A	5/16 "x9 / 32 "
Angle screwdriver set Hexagon, 12-piece	BE-9780	0.050 " , 1/16" , 5/64 " , 3/32" , 7/64 " , 1/8" , 9/64 " , 5/32" , 3/16 " , 7/32" , 1 / 4 " , 5/16 "
Ratchet ring spanner	1320RZ	1 / 4x5 / 16 " , 3 / 8x7 / 16 "
Combination spanner cranked,	1952Z	11/32 " , 1/2" , 9/16 " , 5/8" , 11/16 " , 3/4" , 13/16 " , 7/8" , 15/16 "
Ergo combination pliers, chrome-plated	2628 GC-160IP	160 mm
Ergo	KE18-01	-
Flexible handle 3/8 "	7758	-