

VGA SPLITTER 1-2 350MHz



Duplicate 1 video input to 2 video outputs



METAL SHELL



Features

ITEM	VGA SPLITTER 1-2 350MHz		
INPUT	1X	OUTPUT	2X
TYPE	VGA HD-15P FEMALE	OUTPUT	VGA HD-15P FEMALE
I/O Impedance	75Ω		
HV Channel	Input Level 0.7-5Vp-p		
Max. Bandwidth	350MHz		
Max. Resolution	1920x1440@60Hz		
Support (DDC,DDC2,DDC2B at port 1), VGA, XGA,SVGA,UXGA, Multisync			
TRANS. Distance	65M MAX (External Power Supply is needed); Better under 45M		
Power Plug	INTERCHANGEABLE POWER SUPPLY		
Cascadable	3 Levels; Finally to 8 Displays		
Item Size	130x85x40mm		
Housing	METAL(BLCK AND SILVER OPTIONAL)		
Working TEMP.	Minus 5 to 40 Degree		
Working Humidity	45—80%		