

## Fork-type cable lug - C-FCI 1,5/M4 - 3240034

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Fork-type cable lug, red, 0.5 - 1.5 mm², M4



### Why buy this product

- The fork-type cable lugs without plastic sleeve feature a hard-soldered neck. In conjunction with the CRIMPFOX-RC ... and CRIMPFOX-RCI ... pliers they can be used to achieve maximum conductor pull-out forces
- The insulated versions are halogen-free and feature "EASY ENTRY" technology



### Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 451116
Weight per Piece (excluding packing)	0.68 g
Custom tariff number	85369010
Country of origin	China

### Technical data

#### Dimensions

Length (b)	22 mm
Width (a)	7.2 mm
Length of insulation sleeve (c)	10.5 mm
Inner dimension of the insulating collar (d)	4.1 mm
Inner diameter (f)	4.3 mm
Material thickness (g)	0.75 mm

#### General

Color	red
Stripping length	7 mm
Components	Halogen-free
Inflammability class according to UL 94	V2

# Fork-type cable lug - C-FCI 1,5/M4 - 3240034

## Classifications

eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400201

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052
ETIM 5.0	EC001052

UNSPSC

UNSPSC 6.01	27113201
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

## Drawings

Dimensioned drawing

