



CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

- NOTES:
- "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
 - COUPLING NUT IS CONNECTED TO SHIELD.
 - "/S3056" DESIGNATES SPECIAL WIRING.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	<p>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</p>	DRFT RWC DATE 08/26/08 APVD SCALE 1=1.0 UNIT OF MEASUREMENT MILLIMETER [INCH]	DESCRIPTION E-RKS 8T-264-*--CSM 12/S3056 IDENTIFICATION NO. REV F
MATERIAL SEE SPECIFICATIONS		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		CONTACT TURCK FOR MORE INFORMATION	
FINISH SEE SPECIFICATIONS		DO NOT SCALE THIS DRAWING		FILE: 777023081 SHEET 1 OF 1	

F	UPDATE CABLE OD	CK	09/29/11	35510
REV	DESCRIPTION	BY	DATE	ECO NO.