



ENGLISH

Datasheet

Natural 30m Nylon Air Hose, -40 to +80°C

RS Stock number [415-0418](#)



Description:

Light Duty Nylon Tube

- Suitable for a wide range of light duty applications in compressed air, fuel and oil lines, breather pipe and greasing applications
- Manufactured to BS5409 Part 1 and ISO7628 Part 1 & 2
- 30m coils

Specifications:

Application:	Air Brake, Fuel & Lube Applications, Industrial & Automotive Production Lines, Instrumentation & Secondary Air Systems
Colour:	Natural
Hose Inside Diameter:	7.5mm
Hose Outside Diameter:	10mm
Length:	30m
Manufacturer Series:	NLF
Material:	Nylon
Maximum Operating Pressure:	17 bar
Maximum Operating Temperature:	+80°C
Minimum Operating Temperature:	-40°C