




SPECIFICATION
MATERIALS:
HOUSING & INSERT: PBT
COUPLING: BRASS-NICKEL PLATED
O-RING: VITON
ELECTRICAL:
VOLTAGE: 10-30VDC
CURRENT RATING: 4A PER PORT, 12 AMPS MAX.
PROTECTION CLASS: IP68

NOTES:
THREADED PLUG FITTED TO PORTS 1 & 2 ONLY
PROTECTION CAP FITTED TO ALL M12 PORTS
FIXING HOLES TO SUIT M4 SCREWS

SAP-Nummer	alte Artikel-Nr.	Beschreibung	Farbe
SAP-NUMBER	OLD ENGINEERING-No.	DESCRIPTION	COLOR
1201190028	BKY805P-FBP-03	ULTRA-LOCK MPIS 8 WAY - 16 I/O -3M	gelb/YELLOW
1201190023	BKY805P-FBP-05	ULTRA-LOCK MPIS 8 WAY - 16 I/O -5M	gelb/YELLOW
1201195001	BKY805P-FBP-05A	ULTRA-LOCK MPIS 8 WAY - 16 I/O -5M	gelb/YELLOW
1201148005	BKY805P-FBP-10	ULTRA-LOCK MPIS 8 WAY - 16 I/O -10M	gelb/YELLOW
1201190039	BKY805P-FBP-15	ULTRA-LOCK MPIS 8 WAY - 16 I/O -15M	gelb/YELLOW
1201190040	BKY805P-FBP-20	ULTRA-LOCK MPIS 8 WAY - 16 I/O -20M	gelb/YELLOW

NEW RELEASE EC NO: WEU2010-0220 DRWN:SBH CHKD: APPR:FPACHER	2009/12/07 2009/12/17 2009/12/18	DESCRIPTION	REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION
						MM ONLY		METRIC			
				 =0	mm	INCH	DRAWN BY	DATE	TITLE		
				 =0	4 PLACES ± --- ± ---	SBH 2009/12/10	ULTRA-LOCK MPIS 8 WAY - 16 I/O -XM -PUR				
					3 PLACES ± --- ± ---	CHECKED BY	DATE				
				2 PLACES ± 0.05 ± ---	APPHL_WEU	2009/12/10					
				1 PLACE ± 0.10 ± ---	APPROVED BY	DATE					
					FPACHER	2009/12/17	molex MOLEX INCORPORATED				
					ANGULAR ± --- °		MATERIAL NO.	DOCUMENT NO.	SHEET NO.		
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-120119-023		
A							SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
										1 OF 1	