





F



MOUNTING HOLE DETAIL


E

D



C

B



A

| GENERAL TOLERANCES |       |
|--------------------|-------|
| 10 UNDER           | ±0.2  |
| 10 OVER 30 UNDER   | ±0.25 |
| 30 OVER            | ±0.3  |
| ANGLE              | ±3°   |

|         |           |          |
|---------|-----------|----------|
|         | 5025-02P1 | NO       |
|         | 5025-02P  | YES      |
| EDP NO. | ENG. NO.  | MTG. EAR |

|          |                         |          |      |                           |                                 |                |
|----------|-------------------------|----------|------|---------------------------|---------------------------------|----------------|
|          |                         |          |      | 公差 (Tolerances)           | 所要数                             | DRWG. 9/17/77  |
|          |                         |          |      | .000 → ±0.005 .00 → ±0.05 | (Req)                           | DSN'D H.8/1/77 |
|          |                         |          |      | .0 → ±0.1 . → ±0.3        |                                 | CHK'D 12/8/77  |
|          |                         |          |      | 材料 (MAT'L)                |                                 | APP'D          |
|          |                         |          |      | NYLON 66, 94V-2           |                                 |                |
|          |                         |          |      | 熱処理 (H.T.)                |                                 |                |
|          |                         |          |      | HRc                       |                                 |                |
|          |                         |          |      | 仕上げ (Finish)              |                                 |                |
|          |                         |          |      |                           |                                 |                |
| D        | ADDED -02P1 ECU NO. 917 | 9/17/77  | 1/2  |                           |                                 |                |
| C        | REMOVED "X" ECU NO. 748 | 9/17/77  | 1/2  |                           |                                 |                |
| B        | リブ、パネルスロット、エスケッチ No.    | 12/8/77  | 1/2  |                           |                                 |                |
| A        | REVISED                 | 10/20/77 | 1/2  |                           |                                 |                |
| O        | PROPOSED                | 9/7/77   | 1/2  |                           |                                 |                |
| 記号 (LTR) | 変更内容 (Rev.)             | Date     | Name | Scale 2/1                 | 名称 (Name)                       |                |
|          |                         |          |      |                           | MINI. FIT CONN. 2POS. PLUG HSG. |                |

|                       |      |
|-----------------------|------|
| MOLEX-JAPAN CO., LTD. |      |
| 日本モレックス株式会社           |      |
| No.                   | REV. |
| SD-5025-02P*          | D    |

5

4

3

2

1

F



E

D

C




B

A



パネル板厚 2mm MAX

パネルスロット寸法



## 一般公差

|          |       |
|----------|-------|
| 10未満     | ±0.2  |
| 10以上30未満 | ±0.25 |
| 30以上     | ±0.3  |
| 角度       | ±3°   |

|            |           |          |
|------------|-----------|----------|
| 15-31-1023 | 5025-02P1 | 無        |
| 15-31-1021 | 5025-02P  | 有        |
| EDP NO.    | ENG. NO.  | MTG. EAR |

|                                        |  |             |  |                                 |  |                              |  |
|----------------------------------------|--|-------------|--|---------------------------------|--|------------------------------|--|
| 公差 (Tolerances)                        |  |             |  | 所要数 (Req)                       |  | DRWG. <i>G. Awano 7/7/77</i> |  |
| .000 → ±0.005 .00 → ±0.05              |  |             |  | ★                               |  | DSN'D <i>M. ENO 10/2/77</i>  |  |
| .0 → ±0.1 . → ±0.3                     |  |             |  |                                 |  | CHK'D <i>K. S. Ito</i>       |  |
| 材料 (MAT'L)                             |  |             |  | MOLEX-JAPAN CO., LTD.           |  | REV.                         |  |
| NYLON 66, 94V-2                        |  |             |  | 日本モレックス株式会社                     |  | E                            |  |
| 熱処理 (H.T.)                             |  |             |  | No. SD-5025-02P *               |  |                              |  |
| HRc                                    |  |             |  | 仕上げ (Finish)                    |  |                              |  |
| E REVISED ECN NO. 1499 1/30/79 K.H.    |  |             |  | Scale 2/1                       |  | 名称 (Name)                    |  |
| D ADDED -02P1 ECN NO. 917 7/5/78 4     |  |             |  | MINI. FIT CONN. 2POS. PLUG HSG. |  |                              |  |
| C REMOVED "X" ECN NO. 748 3/18/78 4 VS |  |             |  |                                 |  |                              |  |
| B リブ, パネルスロット, サキット No. 12/16/77 142   |  |             |  |                                 |  |                              |  |
| A REVISED 10/28/77 142                 |  |             |  |                                 |  |                              |  |
| O PROPOSED 7/7/77 142                  |  |             |  |                                 |  |                              |  |
| 記号 (LTR)                               |  | 変更内容 (Rev.) |  | Date                            |  | Name                         |  |