

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

H

REV / 0720-0906-96


21MAR96

LO

ME

1. USE FOR STRIPPED (SINGLE)
WIRE END ONLY

2. WIRE INSUL DIA, 3.78 [.149] MAX



-	100	LOOSE PIECE, BOX	8-328308-1
MS25274/3 CLASS 2	2500	ON TAPE, REEL	2-328308-1
MS25274/3 CLASS 1 & 2	1000	LOOSE PIECE	328308
MILITARY P/N & CLASS	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142


MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F]

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
1.04mm²-2.62mm²
[2,050-5,180]

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [in]



MATERIAL
BODY, CU PER ASTM B152
INSUL, NYLON, COLOR,
BLUE

TOLERANCES UNLESS
OTHERWISE SPECIFIED,

0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-

FINISH
BODY, TIN PLATE
PER MIL-T-10727

DWN 21MAR96

CHK 21MAR96

M ELLIS

APVD 21MAR96

K FERREK

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

SPARE WIRE CAP,
WIRE SIZE, 16-14 AWG

SIZE

CAGE CODE

DRAWING NO

A3

00779

C-328308

SCALE 8:1

SHEET 1 OF 1

REV H