

Retroreflectors



BRT-35DM



BRT-41AHT



BRT-42D



BRT-84



BRT-77X77C



BRT-84X84A



BRT-92X92C



BRT-40X23



BRT-48X32



BRT-35X20AB



BRT-40X19AM

► More Retroreflectors @ www.alliedelec.com

Stock No.	Mfr.'s Type	Reflectivity Factor	Temperature Maximum	Description	EACH
70168879	BRT-1	1.0	60°C	23.0 mm Round Retroreflective Acrylic Target	2.99
70167656	BRT-35DM	1.2	60°C	34.5 mm Round Acrylic Target with Mounting Stud	8.99
70167282	BRT-1.5	1.0	60°C	40.0 mm Round Acrylic Target	3.99
70167671	BRT-41AHT	1.0	200°C	41.0 mm Round, Borosilicate Glass Target	215.95
70167672	BRT-42D	1.0	60°C	42.0 mm Round Acrylic Target with Mounting Stud	4.99
70167675	BRT-84	1.4	60°C	84.0 mm Round Acrylic Target	4.99
70168880	BRT-3	1.0	60°C	84.0 mm Round Acrylic Target	4.99
70167802	BRT-34	1.2	60°C	34.5 mm Round Acrylic Target	5.99
70168881	BRT-2X2	1.0	60°C	51.0 x 51.0 mm Square Black Acrylic Target	4.99
70167674	BRT-77X77C	2.0	60°C	77.0 x 77.0 mm Square Acrylic Target	14.99
70167676	BRT-84X84A	2.0	60°C	84.0 x 84.0 mm Square Acrylic Target	15.99
70167677	BRT-92X92C	3.0	60°C	92.0 x 92.0 mm Square Acrylic Target	16.99
70167670	BRT-40X23	1.4	60°C	40.0 x 23.5 mm Rectangular Acrylic Target	4.99
70167673	BRT-48X32	1.0	60°C	48.0 x 32.5 mm Rectangular Acrylic Target	5.99
70167668	BRT-35X20AB	1.4	60°C	55.0 x 23.5 mm Rectangular Black Acrylic Target	4.99
70167669	BRT-40X19AM	1.2	60°C	60.2 x 19.3 mm Rectangular Acrylic Target	6.99
70168882	BRT-THG-1-100	0.7	60°C	25.0 mm x 2.5 m Retroreflective Tape	24.99
70167305	BRT-THG-2-100	0.7	60°C	50.0 mm x 2.5 m Retroreflective Tape	47.95
70167267	BRT-THG-3-100	0.7	60°C	75.0 mm x 2.5 m Retroreflective Tape	73.95

Mounting Brackets



SMB18A



SMB18SF



SMB18FA



SMBQS18A



SMBQS30L



SMBQ60



SMB55RA



SSA-MBK-EEC3



LMB30RAC



LMBE12RA



SA-E12M30C

► More Mounting Brackets @ www.alliedelec.com

Stock No.	Mfr.'s Type	Used with	Description	EACH
70168883	SMB18A	QS18 (Except AF and FP Models), T18, S18/M18, SM312, and S18U	18 mm, SST Bracket 90°	3.99
70168884	SMB18SF	QS18 (Except AF and FP Models), T18, S18/M18, SM312, and S18U	18 mm, Plastic Swivel Mount Bracket	7.99
70167744	SMB18FA	QS18 (Except FP Models), T18, S18/M18, SM312, and S18U	18 mm, SST Swivel Bracket, Adjustable	10.99
70168888	SMBQS18AF	QS18AF	SST Bracket, Side Mount, 90°	4.99
70167747	SMBQS18A	QS18	Die Cast, Wrap-Around Protective Bracket	5.99
70168885	SMB30MM	QS30, T30, STB, K50, OTB, T30UX, QT50U, TL50, and CL50	30 mm, SST Bracket, 90°	5.99
70168886	SMB30SC	QS30, T30, STB, K50, OTB, T30UX, QT50U, TL50, and CL50	30 mm, Plastic Swivel Mount Bracket	7.99
70167748	SMBQS30L	QS30 (Cabled Models)	SST Bracket, Side Mount	4.95
70168887	SMB312S	SM312	SST Bracket, Side Mount, 90°	4.99
70167743	SMB1815SF	T18, T30, and T30UX	Plastic Swivel Bracket for Mounting by Cable Hub	12.99
70167746	SMBQ60	Q60	Right-Angle, SST Bracket, Side Mount	14.99
70167745	SMB55RA	R58E	15° Offset, SST Bracket	25.99
70248039	SSA-MBK-EEC1	STB, K50, OTB, K50T, TL50, and CL50	30 mm One Station Angle Bracket	35.99
70248070	SSA-MBK-EEC2	STB, K50, OTB, K50T, TL50, and CL50	30 mm Two Station Angle Bracket	44.95
70248071	SSA-MBK-EEC3	STB, K50, OTB, K50T, TL50, and CL50	30 mm Three Station Angle Bracket	53.95
70167320	SMB30A	QS30, T30, STB, K50, OTB, T30UX, QT50U, TL50, and CL50	30 mm SST Bracket, 90°	5.99
70168816	SMB30FA	QS30, T30, STB, K50, OTB, T30UX, QT50U, TL50, and CL50	30 mm SST Bracket, 90°	10.99
70277985	SMBWLS28RA	WLS 28	Standard 90° Angle Bracket, (2) Per Package	2.99
70277986	SMBWLS28SM	WLS 28	Extended 90° Angle Bracket, (2) Per Package	11.99
70274958	LMB30RA	T30, K50, TL50, and CL50	30 mm Sealed Right-Angle Bracket	19.99
70274959	LMB30RAC	T30, K50, TL50, and CL50	30 mm Sealed Right-Angle Bracket	19.99
70277987	LMBE12RA	T30, K50, TL50, and CL50	30 mm x 1/2" NPT Sealed Right-Angle Bracket	24.99
70277988	LMBE12RAC	T30, K50, TL50, and CL50	30 mm x 1/2" NPT Sealed Right-Angle Bracket	24.99
70168338	SA-M30TE12	QS30, T30, STB, K50, OTB, T30UX, QT50U, TL50, and CL50	30 mm Light Base	10.99
70277277	SA-E12M30C	QS30, T30, STB, K50, OTB, T30UX, QT50U, TL50, and CL50	30 mm Mounting Base	14.99
70270944	SOP-E12-150A	QS30, T30, STB, K50, OTB, T30UX, QT50U, TL50, and CL50	150 mm Standoff Pipe	10.99
70277278	SOP-E12-300A	QS30, T30, STB, K50, OTB, T30UX, QT50U, TL50, and CL50	300 mm Standoff Pipe	14.99
70277279	SOP-E12-900A	QS30, T30, STB, K50, OTB, T30UX, QT50U, TL50, and CL50	900 mm Standoff Pipe	26.99