

Datasheet

RS Pro Insulated Crimp Piggyback Terminal, 6.35 x 0.8mm, 1.5mm² to 2.5mm², 16AWG to 14AWG, Blue

RS Stock No: **267-4366**



Product Details

RS Pro insulated crimp piggyback terminal in blue colour has 6.35 x 0.8 mm tab size, 1.5 mm² to 2.5 mm², 16 AWG to 14 AWG wire size. It has a range of insulated piggyback crimp terminals with, a copper sleeved barrel with nylon insulation. This shrouded piggyback crimp wire connectors are colour coded for use with different wire sizes and accept a variety of tab dimensions.

Features and Benefits

- Insulated piggyback crimp terminals with a copper sleeved barrel with nylon or flared vinyl insulation
- Insulated piggyback crimp wire connectors are colour coded for use with different wire sizes and accept a variety of tab dimensions
- Red 0.5 - 1.0 mm², blue 1.5 - 2.5 mm² and yellow 2.5 - 6.5 mm²

**Specifications:**

Colour	Blue
Contact Material	Brass
Insulation	Insulated
Insulation Material	Nylon
Shrouded	Shrouded
Maximum Wire Size (AWG)	14 AWG
Maximum Wire Size (mm ²)	2.5 mm ²
Minimum Wire Size (AWG)	16 AWG
Minimum Wire Size (mm ²)	1.5 mm ²
Overall Length	21.5 mm
Tab Size	6.35 x 0.8 mm
Tab Thickness	0.8 mm
Tab Width	6.35 mm
Wire Size	16 to 14 AWG
Current Rating	10 to 15 A
Temperature Rating	+105°C
Type	Double Crimp
Voltage Rating	600 V