



DCF610S2

10.8V XR Li-Ion Compact Screwdriver

Selling Proposition

- Powerful 10.8V Screwdriver for screwdriving & drilling applications
- Compact, lightweight design
- 15 Position adjustable torque control for consistent screwdriving into a variety of materials with different screw sizes
- Ergonomic handle and rubber overmold to provide ultimate end user comfort
- Parabolic switch profile allowing for greater control over speed of application
- All metal gearing for efficient power transmission and long tool life

Standard Equipment

- 40 min charger
- 2 slide batteries
- Heavy duty kit box

Warranty Specifications

- 30 Day No Risk Satisfaction Guarantee
- 3 Year Limited Warranty
- 1 Year Free Service Contract

Specifications	
Voltage	10.8 V
Battery Capacity	1.5 Ah
Bit Holder	6.35mm
Power Output	154 Watts
No Load Speed	0-1050 rpm
Max Torque	8 Nm
Weight	0.96 kg
Length	158 mm