

558-00370



**Article Number:** 558-00370

**Solid Colored Continuous Roll, 4.0" X 250', Vinyl, Red, 250ft/RL**



## Base Data

**Local Order Number** 558-00370

**Type** HT4RD250

**Color** Red (RD)

**Features and Benefits**

- Continuous Vinyl Labels are made with UV stable materials for long outdoor life.
- Labels are extruded in the actual color and not colored using surface inks for long term fade resistance.
- Continuous Vinyl is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.

**Product Description** HellermannTyton continuous vinyl labels come in a variety of colors and printing widths. The vinyl is UV stable and has been tested to 20 years outdoor durability in Xenon Arc testing. The labels can be printed and cut to any length to create a wide variety custom label designs, on demand and using standard thermal transfer printing equipment. Each roll contains 250 feet (76M) of high performance vinyl.

**Short Description** Solid Colored Continuous Roll, 4.0" X 250', Vinyl, Red, 250ft/RL

## Product Dimensions

**Length L (imperial)** 250.0 ft

**Length L (metric)** 76.2 m

**Width W (imperial)** 4.0 "

**Width W (metric)** 101.6 mm

**Height H (imperial)** 4.0 "

**Height H (metric)** 101.6 mm

**Print Method** Thermal Transfer

**Vertical Repeat VR (imperial)** 4.0 "

**Vertical Repeat VR (metric)** 101.6 mm

**Width of Liner WL (imperial)** 4.0 "

**Width of Liner WL (metric)** 101.6 mm

## Logistics and Packaging

**Quantity per** roll

**Package Quantity (imperial)** 250 ft

**Package Quantity** 76.2 m

**Labels per Column** 1

**Labels per Row** 1

## Material and Specifications

**Material** Vinyl

**Material Shortcut** Vinyl

**Adhesive** Acrylic

**Shortcut Adhesive** Acryl

**Adhesive Operating Temperature** -40 °F to +180 °F (-40 °C to +82 °C)

**Halogenfree** Yes

**Operating Temperature** -40 °F to +180 °F (-40 °C to +82 °C)

**ROHS Conformity** Yes