

Datasheet

1/4 BSPP Male x 1/2 BSPP Female Straight Reducer

RS Stock number [439981](#)



Features

- Maximum working pressure: 250 bar
- Body: Brass
- "O" ring: Technical polymer
- Sealing washer: Technical polymer

Specifications

- Working Temperature: -40 to 150 °C
- Connection 1: 1/4 in BSPP Male
- Connection 2: 1/2 in BSPP Female
- Fitting Direction: Straight
- Fitting Type: Reducer
- Thread Size 1: 1/4in
- Thread Size 2: 1/2in
- Thread Standard 1: BSPP
- Thread Standard 2: BSPP

Measurements

- C1: G1/4
- C2 (mm): G1/2
- E1 (mm): 8
- E2 (mm): 15.6
- F (mm): 27 A/F
- L (mm): 20.5
- Weight (kg): 0.062

