

## Ferrule - A 6 -10 - 3202520

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Ferrule, Length: 10 mm, Color: silver




The figure shows variant A 1-6

### Why buy this product

- The A 0,25.. ferrules can also be used to process 0.14 mm<sup>2</sup> conductors
- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

### Key commercial data

Packing unit	500 pc
Minimum order quantity	500 pc
GTIN	 4 017918 157227
Weight per Piece (excluding packing)	0.2 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	10 mm
Inner dimension of the insulating collar (d)	4.7 mm
Ferrule diameter	3.5 mm
Sleeve wall thickness	0.2 mm

#### Ambient conditions

Max. permanent temperature	105 °C
----------------------------	--------

#### General

Color	silver
-------	--------

# Ferrule - A 6 -10 - 3202520

## Classifications

### eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400201

### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

## Approvals

### Approvals

---

#### Approvals

CSA / CSAus / cCSAus

---

#### Ex Approvals

---

Approvals submitted

---

### Approval details


---

CSAus
-------

## Ferrule - A 6 -10 - 3202520

### Approvals

cCSAus
--------

---