

Ferrule - AI 0,75- 6 GY - 3200690

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Ferrule, Sleeve length: 6 mm, Length: 12 mm, Color: gray




The figure shows the version AI 0,75-8 GY

Why buy this product

- The AI 0,25.. ferrules can also be used to process 0.14 mm² conductors
- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper
- The insulation reliability of close connections is increased and the splicing of wires is prevented



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| GTIN |  4 017918 094287 |
| Weight per Piece (excluding packing) | 0.08 g |
| Custom tariff number | 85369010 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--|---------|
| Length (b) | 12 mm |
| Sleeve length | 6 mm |
| Inner dimension of the insulating collar (d) | 2.8 mm |
| Ferrule diameter | 1.3 mm |
| Insulating collar thickness | 0.25 mm |
| Sleeve wall thickness | 0.15 mm |

Ambient conditions

| | |
|----------------------------|--------|
| Short-term temperature | 120 °C |
| Max. permanent temperature | 105 °C |

Ferrule - AI 0,75- 6 GY - 3200690

Technical data

General

| | |
|---|--------------------------------|
| Color | gray |
| Components | free from silicone and halogen |
| Inflammability class according to UL 94 | HB |
| Material | E-CU |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060701 |
| eCl@ss 4.1 | 27060701 |
| eCl@ss 5.0 | 27400201 |
| eCl@ss 5.1 | 27400201 |
| eCl@ss 6.0 | 27400201 |
| eCl@ss 7.0 | 27400201 |
| eCl@ss 8.0 | 27400201 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000005 |
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121703 |

Approvals

Approvals

Approvals

CSA / CSAus / cCSAus

Ex Approvals

Approvals submitted

Ferrule - Al 0,75- 6 GY - 3200690

Approvals

Approval details

CSA 

CSAus

cCSAus

Drawings

Dimensioned drawing

