

## Housing - HC-HV 3-AML - 1773569

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON panel mounting base HV3, with single locking latch, height 27 mm



### Key commercial data

Packing unit	10 pc
GTIN	 4 017918 037758
Weight per Piece (excluding packing)	99.52 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Height	27 mm
Width	43 mm
Length	93 mm
Length of the assembly cutout	64 mm
Width of the assembly cutout	35 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HV-HV3
Type	HV3
Housing type	Panel mounting base
Locking type	With single locking latch
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray

# Housing - HC-HV 3-AML - 1773569

## Technical data

### General

Material lock	Stainless steel, handle: PA
Material grip body interlock	PA

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

# Housing - HC-HV 3-AML - 1773569

## Approvals

EAC

## Drawings

Dimensioned drawing

