

PC-RG6-7

ABB contact for United
Kingdom

General Information

Extended Product Type:	PC-RG6-7
Product ID:	1SNA519104R0700
EAN:	3472599857605
Catalog Description:	PC-RG6-7 Lateral Jumper Bar - 7 poles - Orange
Long Description:	PC-RG6-7 Ring lug Lateral Jumper Bar - 7 poles

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Lateral Jumper Bars

Ordering

EAN:	3472599857605
Minimum Order Quantity:	5 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	3.1 mm
Product Net Height:	71.6 mm
Product Net Length:	26.7 mm
Product Net Depth:	26.7 mm
Product Net Weight:	13.92 g

Container Information

Package Level 1 Units:	5 piece
Package Level 1 Width:	80 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	58 mm
Package Level 1 Gross Weight:	0.07650 kg
Package Level 1 EAN:	3472599857605
Package Level 2 Units:	300 piece
Package Level 2 Width:	230 mm
Package Level 2 Height:	230 mm
Package Level 2 Length:	350 mm
Package Level 3 Units:	9600 piece

Environmental

Ambient Air Temperature:	Operation -40...+100 °C Storage -40...+100 °C
---------------------------------	--

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Flammability According to UL94:	V2

Additional Information

Ambient Temperature:	-25...+70 °C
Color:	Orange
Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Product Main Type:	PC-RG6
Product Name:	Terminal Blocks Accessories

Rated Current (I_n):	Main Circuit 41 A
Rated Voltage (U_r):	800 V
RoHS Date:	20110721
Spacing:	11 mm

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225158C1000
RoHS Information:	1SND230547F0200

Classifications

ETIM 4.0:	EC000489 - Cross-connector for terminal block
ETIM 5.0:	EC000489 - Cross-connector for terminal block

