

# Datasheet

## LED 24W Task Light



### Description

This LED task light is ideal for all site lighting requirements. Cool running which eliminates fire hazards associated with halogen versions, and with a protective rubber trim.

### Features

- Super bright LED – Daylight (6000K)
- Die cast aluminium body with steel stand
- Tilttable head and carry handle
- Protective rubber trim
- Can be used with S1020 tripod
- 3m cable length
- Rated life of 30,000 hours
- 3 year guarantee

### Range

110V 24W LED Task Light                      842-8162

### Dimensions (mm)

	Height	Width	Depth
842-8162	305	235	160

### Technical Specification

Voltage	110V~ 50Hz
Lamp Type	SMD LED
Wattage	24W
Lamp Col. Temp	6000K
Lumen Output	2000lm
IP Rating	IP44

### Standards

- BS EN 60598-1:2008 +A11:2009
- BS EN 60598-2-5:1999
- BS EN 61347-1:2008
- BS EN 61347-2-13:2006
- BS EN 55015:2006 +A2:2009
- BS EN 61547:2009
- BS EN 61000-3-2:2006 +A2:2009
- BS EN 61000-3-3:2008
- BS EN 60309:1999