

CyMotion EXPERT



Models may vary from the image shown

The ideal keyboard for anyone who values reliability and perfect handling without superfluous show effects

Coffee on the keyboard... dirt between the keys... life is hard, but the CyMotion can take all this and more!

Thanks to its special construction, this capable, extremely robust cabled keyboard in the new, elegant CyMotion design is nearly indestructible and offers reliable top performance and precise actuation even after many years.

Perfect ergonomics and numerous clever additional features are other convincing arguments.

Key benefits

- extremely robust and long-lived
- Not sensitive to dirt and liquids
- compact, symmetrical design
- 8 additional HotKeys, KeyM@n-key and second function layer for F keys to control multimedia and internet functions.
- 20 % larger key surface
- USB- or PS/2 connection
- consistently precise keystroke
- Advanced Keyboard Technologie

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

approx. 880 g

Total weight (with packaging):

approx. 1200 g

Cable Length:

approx. 1.80 m

Storage Temperature:

-20°C to 60°C

Operating Temperature:

0°C to 50°C

Current Consumption:

typ. 16 mA

Interface:

- USB (PS/2 via adapter)

Product approvals:

- FCC DoC 
- cURus 
- VDE GS 
- c-tick 
- VCCI 
- CE 

System requirements:

- USB or PS/2 connection

Delivery Volume:

- CyMotion EXPERT
- Printed instructions
- Adapter (USB socket on PS/2 plug)

Dimensions (product):

approx. 462 x 175 x 36 mm

Packaging dimensions:

approx. 520 x 232 x 42 mm

Keyboard:

- Key technology: ATK
- Service life, standard key: > 20 million key operations
- Operation characteristics: Soft pressure point
- Inscription technology: Laser
- Inscription layout: Standard
- Number of Keys: Product dependant, see table "Models"

Packaging Unit:

- Number of products in the master package: 11
- Number of master packages per pallet: 12

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Number of Keys
1	CyMotion EXPERT	G86-22000BBADA B	4025112069314	Bulgaria	black	black	105+9
2	CyMotion EXPERT	G86-22000BBAEA B	4025112068119	Bulgaria	light grey	light grey	105+9
3	CyMotion EXPERT	G86-22000BEADA B	4025112052309	Belgium	black	black	105+9
4	CyMotion EXPERT	G86-22000BEAEA B	4025112052200	Belgium	light grey	light grey	105+9
5	CyMotion EXPERT	G86-22000CHADA B	4025112052316	Switzerland	black	black	105+9
6	CyMotion EXPERT	G86-22000CHAEA B	4025112052217	Switzerland	light grey	light grey	105+9
7	CyMotion EXPERT	G86-22000DEADA B	4025112052323	Germany	black	black	105+9
8	CyMotion EXPERT	G86-22000DEAEA B	4025112052224	Germany	light grey	light grey	105+9
9	CyMotion EXPERT	G86-22000DKAEA B	4025112057359	Denmark	light grey	light grey	105+9
10	CyMotion EXPERT	G86-22000ESADA B	4025112052330	Spain	black	black	105+9
11	CyMotion EXPERT	G86-22000ESAEA B	4025112052231	Spain	light grey	light grey	105+9
12	CyMotion EXPERT	G86-22000EUADA B	4025112052347	US English with EURO symbol	black	black	104+9
13	CyMotion EXPERT	G86-22000EUAEA B	4025112052248	US English with EURO symbol	light grey	light grey	104+9
14	CyMotion EXPERT	G86-22000FRADA B	4025112052354	France	black	black	105+9
15	CyMotion EXPERT	G86-22000FRAEA B	4025112052255	France	light grey	light grey	105+9
16	CyMotion EXPERT	G86-22000GBADA B	4025112052361	UK	black	black	105+9
17	CyMotion EXPERT	G86-22000GBAEA B	4025112052262	UK	light grey	light grey	105+9
18	CyMotion EXPERT	G86-22000GRAEA B	4025112064623	Greece	light grey	light grey	105+9
19	CyMotion EXPERT	G86-22000ITADAB	4025112052378	Italy	black	black	105+9
20	CyMotion EXPERT	G86-22000ITAEAB	4025112052279	Italy	light grey	light grey	105+9
21	CyMotion EXPERT	G86-22000NOAEA B	4025112074691	Norway	light grey	light grey	105+9
22	CyMotion EXPERT	G86-22000RGADA B	4025112052385	US / Cyrillic	black	black	104+9

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Number of Keys
23	CyMotion EXPERT	G86-22000RGAEA B	4025112052286	US / Cyrillic	light grey	light grey	104+9
24	CyMotion EXPERT	G86-22000RIAEAB	4025112059896	Italian / Cyrillic	light grey	light grey	105+9
25	CyMotion EXPERT	G86-22000SLADA B	4025112052392	Slovenia	black	black	105+9
26	CyMotion EXPERT	G86-22000SLAEAB	4025112052293	Slovenia	light grey	light grey	105+9
27	CyMotion EXPERT	G86-22000TQAEA B	4025112060731	Turkey	light grey	light grey	105+9