


| SPECIFICATIONS                    |                                   |
|-----------------------------------|-----------------------------------|
| CONTACT CARRIER MATERIAL          | TPU                               |
| MOLDED HEAD MATERIAL/COLOR        | TPU/YELLOW                        |
| CONTACT MATERIAL/PLATING          | BRASS/GOLD                        |
| COUPLING NUT MATERIAL/PLATING     | BRASS/NICKEL                      |
| RATED CURRENT [A]                 | 2.0 A                             |
| RATED VOLTAGE [V]                 | 60 VAC/75 VDC                     |
| OUTER CABLE JACKET MATERIAL/COLOR | TPU/GRAY                          |
| CONDUCTOR INSULATION MATERIAL     | PVC                               |
| NUMBER OF CONDUCTORS [AWG]        | 10x24 AWG                         |
| TEMPERATURE RANGE                 | -40°C to +90°C (-40°F to +194°F)  |
| PROTECTION CLASS                  | NEMA 1,3,4,6P AND IEC IP68, IP69K |



| CABLE LENGTH                 | TOLERANCE*                                                                  |
|------------------------------|-----------------------------------------------------------------------------|
| ALL LENGTHS                  | + 4% (OR 50mm) OF LENGTH<br>- 0% (OR 0mm) OF LENGTH<br>WHICHEVER IS GREATER |
| STRIP LENGTH                 | TOLERANCE*                                                                  |
| 0-7mm                        | ±0.5mm                                                                      |
| 8-29mm                       | ±1.0mm                                                                      |
| 30-49mm                      | ±2.0mm                                                                      |
| 50-69mm                      | ±3.0mm                                                                      |
| 70-100mm                     | ±4.0mm                                                                      |
| OVER 100mm                   | ±5.0mm                                                                      |
| * UNLESS OTHERWISE SPECIFIED |                                                                             |

- NOTES:
- "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
  - "/S90" DESIGNATES THERMOPLASTIC POLYURETHANE (TPU) CABLE JACKET.

**SOURCE DRAWING - FOR REFERENCE ONLY**

|                                           |                                                                 |                                                                                                                            |                                                                                                                                                                                                                                        |                                                                                           |
|-------------------------------------------|-----------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|
| RELATED DOCUMENTS<br>1.<br>2.<br>3.<br>4. | 3RD ANGLE PROJECTION<br>                                        | THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. | <div style="text-align: center;"> <p><b>TURCK INC</b><br/>High Technology Sensors and Automation Controls</p> </div> 3000 CAMPUS DRIVE<br>MINNEAPOLIS, MN 55441<br>1-800-544-7769<br>(763) 553-7300<br>(763) 553-0708 fax<br>turck.com | DRFT RWC    DATE 04/25/06<br>APVD    SCALE 1=1.0<br>DESCRIPTION<br>RKC 10T-*--RSC 10T/S90 |
| MATERIAL<br>SEE SPECIFICATIONS            | ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY | UNIT OF MEASUREMENT<br><b>MILLIMETER [ INCH ]</b>                                                                          | IDENTIFICATION NO.                                                                                                                                                                                                                     | REV<br>G                                                                                  |
| FINISH<br>SEE SPECIFICATIONS              |                                                                 | CONTACT TURCK FOR MORE INFORMATION                                                                                         | DO NOT SCALE THIS DRAWING                                                                                                                                                                                                              | FILE: 777012641                                                                           |

|     |                  |     |          |         |
|-----|------------------|-----|----------|---------|
| G   | UPDATE TEMP SPEC | RDS | 01/10/13 | 40914   |
| REV | DESCRIPTION      | BY  | DATE     | ECO NO. |