

## Classic ECO Ball

Classic ECO Ball 28W E27 230V Sleeve

**0023746**



### Range features

- 1:1 replacement of Incandescent Ball lamp
- More efficient - more savings
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Sparkling light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- 100% dimmable
- Average rated life 2000 hrs - up to two times more average life compared to incandescent lamps



### PRODUCT OVERVIEW

Light colour	828 Homelight
Technology	Halogen
Ordering number	0023746
Average life (Rated) (h)	2000
Energy class	D
Lamp shape	Ball
Lamp finish	Clear
Dimmable	Yes
Cap/Base	E27
Type	Ball ECO
EAN code	5410288237466
CRI (Ra)	100
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	370
Watt (Nominal) (W)	28
Equivalent watt (W)	37
Voltage (V)	230

## Classic ECO Ball

Classic ECO Ball 28W E27 230V Sleeve

0023746

### DATA TABLE

#### General data

Ordering number	0023746
Technology	Halogen
Average life (Rated) (h)	2000
Average life (Nominal) (h)	2000
Energy saving lamp	No
Energy class	D
Lamp finish	Clear
Lamp shape	Ball
Dimmable	Yes
Cap/Base	E27
Type	Ball ECO
EAN code	5410288237466
Long description	1:1 replacement of Incandescent Ball lamp. More efficient - more savings. Excellent colour rendering (CRI = 100). Instant illumination. Sparkling light output. Less heat generation than incandescent lamp. Less CO2 emissions. Identical shape as standard incandescent lamp. Commercial and domestic application. 100% dimmable. Average rated life 2000 hrs - up to two times more average life compared to incandescent lamps
Product name	Classic ECO Ball 28W E27 230V Sleeve
Lamp mercury content (mg)	0
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Control gear required	No
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-2
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 8000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

#### Optical data

Light colour	828 Homelight
CRI (Ra)	100
Suitable for accent lighting	No
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	370
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	370

# Classic ECO Ball

*Classic ECO Ball 28W E27 230V Sleeve*

**0023746**

## Electrical data

<b>kWh per 1000 hours burning time</b>	28
<b>Watt (Rated) (W)</b>	28
<b>Watt (Nominal) (W)</b>	28
<b>Equivalent watt (W)</b>	37
<b>Voltage (V)</b>	230
<b>Lamp power factor</b>	1

## Physical data


<b>Lamp Length (mm) - C/L</b>	74
<b>Lamp Diameter (mm) - D</b>	46
<b>Packaging outer width (cm)</b>	25
<b>Packaging outer length (cm)</b>	48.5
<b>Packaging outer height (cm)</b>	17.5
<b>Packaging single width (cm)</b>	4.55
<b>Packaging single length (cm)</b>	4.55
<b>Packaging single height (cm)</b>	7.6

## Classic ECO Ball

Classic ECO Ball 28W E27 230V Sleeve

0023746

### TECHNICAL DRAWINGS



### ENERGY LABEL

