

Screw connection - WP-GT PP HF PG9 - 3241003

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable gland made from PP with Pg thread, rotatable, IP54 protection

The figure shows the WP-GT PP HF M10 version



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 711357
Weight per Piece (excluding packing)	3.54 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	39.5 mm
Width (a)	21 mm
Wrench size	19.00 mm
Outside diameter	14.00 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 110 °C
Degree of protection	IP54

General

Color	gray
Type	Rotatable
	Outer thread
Components	Halogen-free

Screw connection - WP-GT PP HF PG9 - 3241003

Technical data

General

Inflammability class according to UL 94	HB
Material	PP

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27149109

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

VDE Zeichengenehmigung


Ex Approvals

Approvals submitted

Approval details

Screw connection - WP-GT PP HF PG9 - 3241003

Approvals

VDE Zeichengenehmigung 

Accessories

Accessories

Corrugated pipe

Protective hose - WP-SPIRAL PVC C 14 - 3240850



Protective hose, spring steel wire with PVC coating, highly stranded, 1 Pcs. / Pkt. = roll à 10 m

Protective hose - WP-SPIRAL PU C HF 14 - 3240857



Protective hose, spring steel wire with PU coating, highly stranded, 1 Pcs. / Pkt. = roll à 10 m
