


TOLERANCES (UNLESS SPECIFIED)	
0-10mm	±0.2mm
10.1-50mm	±0.5mm
50.1-250mm	±1.0mm
>250mm	±2.0mm



FLOOR MOUNTING TRANSFORMER

TYPE: ISOLATION TRANSFORMER

INPUT: 400V 50Hz

OUTPUT: 55-0-55V

RATING: CENTER TAP EARTHED

ENCLOSURE: 10KVA CONTINUOUS

COLOUR: MILD STEEL

RATED IP22

RAL 7032

REV	4	
	3	
	2	
	1	

CARROLL & MEYNELL
 TRANSFORMERS LIMITED
 TEL: 01642 617406 FAX: 01642 614178
 enquiries@carroll-meynell.com

TITLE	FLOOR MOUNTING TRANSFORMER
	CM10000/FM0/400
	ALL DIMENSIONS IN mm

DRAWN	PROJECTION	DATE	SCALE
GB		26/4/8	NTS
DRAW No	REV	PAGE	
3289	1	1/1	