

Rittal – North American Industrial Buyer's Guide



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

WM - Wallmount

Depth: 12 - 20" (300 - 500 mm), Height: 36 - 60" (900 - 1500 mm)

Wallmount

Carbon Steel

| | | | | | | | |
|--------------------------------|----|-------------------|-------------------|-------------------|-------------------|-------------------|------|
| Height (H1) inches (mm) | PU | 36 (900) | 36 (900) | 36 (900) | 36 (900) | 36 (900) | Page |
| Width (B1) inches (mm) | | 30 (760) | 36 (900) | 42 (1050) | 47 (1200) | 60 (1500) | |
| Depth (T1) inches (mm) | | 12 (300) | 12 (300) | 12 (300) | 12 (300) | 12 (300) | |
| Panel Height (G1) inches (mm) | | 34 (870) | 34 (870) | 33 (850) | 33 (850) | 33 (850) | |
| Panel Width (F1) inches (mm) | | 28 (704) | 33 (840) | 39 (1000) | 45 (1150) | 57 (1450) | |
| Part No. | 1 | WM363012NC | WM363612NC | WM364212NC | WM364812NC | WM366012NC | |
| Door(s) | | 1 | 1 | 2 | 2 | 2 | |
| Weight lb (kg) | | 120 (55) | 140 (64) | 167 (76) | 186 (85) | 226 (103) | |

Accessories

| | | | | | | |
|-------------------|---|----------|--------|---|---|-----|
| Wallmount bracket | 4 | 2508.200 | | | | 253 |
| Handle | 1 | 2533.000 | WMLHKL | | | 219 |
| Dead front kit | 1 | DFK3636C | - | - | - | 230 |

| | | | | | | | |
|--------------------------------|----|-------------------|-------------------|-------------------|-------------------|-------------------|------|
| Height (H1) inches (mm) | PU | 42 (1050) | 42 (1050) | 47 (1200) | 47 (1200) | 60 (1500) | Page |
| Width (B1) inches (mm) | | 36 (900) | 60 (1500) | 36 (900) | 47 (1200) | 36 (900) | |
| Depth (T1) inches (mm) | | 12 (300) | 12 (300) | 12 (300) | 12 (300) | 12 (300) | |
| Panel Height (G1) inches (mm) | | 40 (1020) | 39 (1000) | 45 (1155) | 45 (1150) | 57 (1455) | |
| Panel Width (F1) inches (mm) | | 33 (840) | 57 (1450) | 33 (840) | 45 (1150) | 33 (840) | |
| Part No. | 1 | WM423612NC | WM426012NC | WM483612NC | WM484812NC | WM603612NC | |
| Door(s) | | 1 | 2 | 1 | 2 | 1 | |
| Weight lb (kg) | | 169 (77) | 259 (118) | 180 (82) | 204 (93) | 200 (91) | |

Accessories

| | | | | | | | |
|-------------------|---|----------|---|----------|----------|----------|-----|
| Wallmount bracket | 4 | 2508.200 | | | | 253 | |
| Handle | 1 | WMLHKL | | | 2533.000 | WMLHKL | 219 |
| Dead front kit | 1 | DFK4236C | - | DFK4836C | - | DFK6036C | 230 |

| | | | | | | | |
|--------------------------------|----|-------------------|-------------------|-------------------|-------------------|-------------------|------|
| Height (H1) inches (mm) | PU | 36 (900) | 47 (1200) | 60 (1500) | 30 (760) | 47 (1200) | Page |
| Width (B1) inches (mm) | | 30 (760) | 36 (900) | 36 (900) | 24 (600) | 36 (900) | |
| Depth (T1) inches (mm) | | 16 (400) | 16 (400) | 16 (400) | 20 (500) | 20 (500) | |
| Panel Height (G1) inches (mm) | | 34 (870) | 45 (1155) | 57 (1450) | 29 (730) | 45 (1155) | |
| Panel Width (F1) inches (mm) | | 28 (704) | 33 (840) | 33 (840) | 22 (549) | 33 (840) | |
| Part No. | 1 | WM363016NC | WM483616NC | WM603616NC | WM302420NC | WM483620NC | |
| Door(s) | | 1 | 1 | 1 | 1 | 1 | |
| Weight lb (kg) | | 134 (61) | 204 (93) | 210 (95) | 85 (39) | 212 (96) | |

Accessories

| | | | | | | | |
|-------------------|---|----------|----------|----------|----------|----------|-----|
| Wallmount bracket | 4 | 2508.200 | | | | 253 | |
| Handle | 1 | 2533.000 | WMLHKL | | | 219 | |
| Dead front kit | 1 | DFK3630C | DFK4836C | DFK6036C | DFK3024C | DFK4836C | 230 |

Inch and pound measurements are rounded to the nearest whole number.