



GE  
Lighting



PY21W basic

TU 1056 E1 PY21W 12V BAU15S GE MIH

**17248**

---

## Product information

Single filament incandescent lamp for vehicle external lighting applications.

---

## Product data

Cap/Base	BAU15s
Bulb Shape	Spherical
Bulb Diameter [mm]	26.5
Maximum Overall Length [mm]	52.5
Net weight per piece [g]	9
Gross weight per piece [g]	11
Brand	General Electric (GE)

## Performance data

Colour (product colour)	AMBER
Nominal lumens [lm]	280
Nominal power [W]	21
Nominal lamp voltage [V]	12

## Electrical data

Lamp Current [A]	1.896
Ballast Required	No

## Logistic data

DUN Code	20043168172480
EAN Code	9004102328193
Pack Quantity	200
Layer quantity	4000 EUR, 4800 UK
Layer quantity EUR	4000
Layer quantity UK	4800
Pallet quantity EUR (PC)	20000
Pallet quantity UK (PC)	24000
Outer case size	291 x 146 x 206 (mm)
Product status	Available

## Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Automotive Lamps - Catalogue \(PDF\)](#)

[Motorcycle Lamp Guide - Brochure \(EN\) \(PDF\)](#)