


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.



- 1 WIRE INSULATION DIA. = .115-.170
2 TONGUE MATERIAL THK. = .031 ± .002
3 TIN PL. (MIL-T-10727) .0001 MIN. EXT THK.
4 FOREIGN PRODUCTION ONLY

REVISIONS

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	✓		J	REDRAWN-REV. PER G-1475, G-1175, P85-0045 & P85-0046	1/9/80	Bm
✓	✓		K	REV G-2348	DAP 4-87	Bm
✓	✓		L	OBS. 2--3 PER G-3358	4-25-88	28/44
✓	✓		M	OBSOLETE 2--2 PER G-4247	ST 10/14/88	AG
✓	✓		N	REV. PER G-3879	DKS 12-88	44
✓	✓		P	OBS. 1--1 G-3729	DKS 1-24-89	44

OBSOLETE
OBSOLETE
OBSOLETE

100	ON TAPE, SM. BOX	2-31906-3
1000	ON TAPE, LG. BOX	2-31906-2
4000	ON TAPE, REEL	1-31906-1
4	LOOSE PIECE	31906

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .002 ANGLES ±		CONTRACT NO DR UTA / RFB 9-18-85 CHK P. Mutyaleen 1/9/86 APPD J. L. L. 1/10/86 APPD DSGN APPD OTHER APPD		AMP INCORPORATED Harrisburg, Pa.	
MATERIAL INSULATION: PVC - BLUE BODY & SLEEVE: COPPER (QG-C-576)		NAME TERMINAL P.I.D.G., RING TONGUE WIRE SIZE: 16-14		DRAWING NO 31906	
FINISH BODY-3		SIZE B	FSCM NO 00779	SHEET 1 OF 1	
		SCALE NTS			