

Header - PTSM 0,5/ 2-HH0-2,5-SMD WH R32 - 1814919

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Header, Nominal current: 6 A, Rated voltage (III/2): 250 V, Number of positions: 2, Pitch: 2.5 mm, Color: White, Contact surface: Tin, Assembly: Taped SMD/THT/THR components



Key commercial data

Packing unit	1 PCE
Minimum order quantity	600 PCE
GTIN	 4 046356 761123
Custom tariff number	85369010
Country of origin	GERMANY

Technical data

Dimensions

Length	7.5 mm
Height	5 mm
Pitch	2.5 mm
Dimension a	2.5 mm

General

Range of articles	PTSM 0,5/..-HH-SMD
Insulating material group	I
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	125 V
Rated voltage (III/2)	250 V
Rated voltage (II/2)	320 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	6 A

Header - PTSM 0,5/ 2-HH0-2,5-SMD WH R32 - 1814919

Technical data

General

Maximum load current	6 A
Insulating material	PA
Inflammability class according to UL 94	V0
Color	White

Classifications

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002637

UNSPSC

UNSPSC 11	39121432
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432
UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432

eCl@ss

eCl@ss 4.0	27141109
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 7.0	27440401