


STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061313-Y	XY.0

2	BLANK LABEL	5
1	SC CONNECTOR, MM, DUPLEX HOUSING, RET. PLATE HALF, BEIGE	4
1	SC CONNECTOR, MM, DUPLEX HOUSING, BEAM HALF, BEIGE	3
1	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE	2
L	FOCAB 1.8MZ 62.5/125, GREY, LSZH	1
Qty	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 160CT2009	 Tyco Electronics Corporation 's-Hertogenbosch, Nederland		
DIMENSIONS: mm		CHK A. HENGELMOLEN 160CT2009	NAME FIBER OPTIC LEAD 1.8MZ LC/DPX – SC/DPX MULTI MODE 62.5/125		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. HENGELMOLEN 160CT2009			
		PRODUCT SPEC —			
0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –		APPLICATION SPEC —			
MATERIAL —		WEIGHT —			
FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C-2061313	RESTRICTED TO —
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1	REV A