

EK EKMB 130 G



Sample photo

Order symbol: EKMB 130 G
Product nbr: 2538019
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013507
EI. number:
 Finland: 3425409
 Electric No. Italy: 7501025
 Electric No. Sweden: 2538019

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	380	190	130	EKMR	Base, PC
inch:	15.0	7.5	5.1	EKM 30-G	Cover
Materials:				EKM 80-G	Cover
Material:	Polycarbonate			EKM 30-T	Cover
Base colour:	RAL 7035 -light grey			EKM 80-T	Cover
Cover screws material:	Polyamide			EKMVT	Mounting plate
Cover colour:	RAL 7035 -light grey			EKMXT	Mounting plate isolated
Cover screws colour:	Grey			EKV 12	DIN-35 Mounting rail
Gasket material:	Polyurethane			EKV 32	DIN-35 Mounting rail
				EKMZR	Extension frame
Temperatures:				Rating:	
Temperature °C (short term):	-40 ... 120 °C			Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK08	
Temperature °F (short term):	-40 ... 250 °F			Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
Accessories:				Certificates:	
EKMB	Base, PC			SGS Fimko	
				Gost R	

