

## Trend Spot

TREND SPOT LED MONO BA 36° 830

0053385



### Range features

- Integrated LED luminaire with LED driver
- 540 lumen output / 10W
- Beam Angle 30° / 3000K Warm White
- High quality aluminium construction
- Multi-directional 25° tilt
- High Powered Single LED – 10W
- Size 97x97mm. Cutout: 90mm
- Halogen optical effect
- Extra long life – 50,000hrs
- Available in white and brushed aluminium

LED

## PRODUCT OVERVIEW

Ordering number	0053385
Light colour	Warm white
Technology	LED
Average life (Rated) (h)	50000
EAN code	5410288533841
Certifications	ENEC
Mount	Ceiling recessed
Housing	Steel
CRI (Ra)	90
LOR (%)	100
Beam angle(°)	30
Efficacy (Rated) (lm/w)	54
Voltage (V)	220-240
Colour	Brushed Aluminium
IP rating	20
IK rating	02

## Trend Spot

TREND SPOT LED MONO BA 36° 830

0053385

### DATA TABLE

#### General data

<b>Technology</b>	LED
<b>Ordering number</b>	0053385
<b>Average life (Rated) (h)</b>	50000
<b>EAN code</b>	5410288533841
<b>Certifications</b>	ENEC
<b>Mount</b>	Ceiling recessed
<b>Long description</b>	Integrated LED luminaire with LED driver. 540 lumen output / 10W. Beam Angle 30° / 3000K Warm White. High quality aluminium construction. Multi-directional 25° tilt . High Powered Single LED – 10W. Size 97x97mm. Cutout: 90mm. Halogen optical effect . Extra long life – 50,000hrs. Available in white and brushed aluminium
<b>Product name</b>	TREND SPOT LED MONO BA 36° 830
<b>Control gear type</b>	External
<b>Environment</b>	Interior
<b>General application</b>	Residential accent down lighting
<b>Housing</b>	Steel

#### Optical data

<b>Light colour</b>	Warm white
<b>CRI (Ra)</b>	90
<b>LOR (%)</b>	100
<b>Beam angle(°)</b>	30
<b>Luminous flux (Nominal) (lm)</b>	540
<b>Distribution type</b>	Direct

#### Electrical data

<b>Efficacy (Rated) (lm/w)</b>	54
<b>Voltage (V)</b>	220-240
<b>Drive current (mA)</b>	800mA
<b>Electrical protection</b>	CLASS II

# Trend Spot

TREND SPOT LED MONO BA 36° 830

**0053385**

## Physical data

<b>Weight (kg)</b>	0.5
<b>Colour</b>	Brushed Aluminium
<b>Lamp included</b>	Yes
<b>Height (mm)</b>	50
<b>Width (mm)</b>	97
<b>Length (mm)</b>	97
<b>IP rating</b>	20
<b>IK rating</b>	02
<b>Vertical tilt (°)</b>	25
<b>Horizontal rotation (°)</b>	25
<b>Cutout diameter (mm)</b>	85 ø
<b>Cutout shape</b>	Square
<b>Recessed depth (mm)</b>	50
<b>Diffuser finish</b>	Unique LED optic - creates halogen feel and look

## Trend Spot

TREND SPOT LED MONO BA 36° 830

0053385

### TECHNICAL DRAWINGS



### ENERGY LABEL

