



Main

| | |
|-------------------|----------------------------------|
| Range of product | Opale Pragma D |
| Device short name | Distri'clicXE distribution block |

Complementary

| | |
|-------------------------------|-------------------------------------|
| [In] rated current | 63 A (40 °C) |
| [Ui] rated insulation voltage | 250 V AC |
| 9 mm pitches | 26 |
| Connections - terminals | Cable connectors 16 mm ² |

Environment

| | |
|--------------------------|-----------|
| RoHS EUR conformity date | 0643 |
| RoHS EUR status | Compliant |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.