

Datasheet

RS Pro Straight Cable Mount FME Connector, Plug, Crimp Termination, 50 Ω , RG58/U

RS Stock No: **738-5737**



Product Details

RS Pro cable mount connector jack is designed for 50 Ω impedance applications. This straight, FME connector is compatible with RG58/U cable and offers crimp termination. The gold plated brass contact ensures superior connectivity.

Features and Benefits

- Suitable for applications such as mobile equipment and installations
- Gold plated brass contacts
- Nominal impedance 50 Ω

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Cable Type	RG58/U
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	0 to 900 MHz
Termination Method	Crimp
Dimensions	29.2 x 7.5 mm
Operating Temperature Range	-55 to +125°C