

PT-E100VP

brother®
at your side



PT-E100VP Electronic Labeller

Create professional, durable, laminated labels for cables, faceplates, consumer units and other electrical and datacom installations.

- Dedicated functions to create the most common label types
- 168 symbols including common electrical/datacom symbols
- Includes tape cassette, AC adapter and carrying case
- Prints 3.5, 6, 9, 12mm labels



LABELS THAT STICK.

P-touch

PT-E100VP

The P-touch E100VP is a lightweight, handheld industrial labeller developed with easy-to-use functions for creating common label types quickly and easily. Complete with a practical carrying case to hold the bundled AC adapter. There is also space for additional tape cassettes including strong-adhesive and flexible-ID tapes, which have been specially developed for use by electricians and other professionals.

Fast 20mm/second print speed

Get the job done quickly by printing each label in just a few seconds.



Cable wrap

Identify cables quickly with easy-to-read labels.



Cable flag

Select your cable diameter to print the correct length of label.



168 built-in symbols

Includes common electrical, datacom, AV, security and safety symbols.



Technical Specifications

Hardware

Housing dimensions (mm)	110(W) x 207(H) x 59(D)
Housing weight	390g
Tape size	TZe tape: 3.5, 6, 9, 12mm
Print resolution	180 dpi
Max. print height	9.0 mm
Max. print speed	20mm / sec
Cutter type	Manual: Cutter blade
Keyboard type	ABC with numeric keypad
Number of keys	54 keys
LCD display	16 characters x 1 line graphic
LCD size	58 mm x 22 mm
Print preview	Yes
Text buffer	Max 80 chrs
Label memory	720 chrs (9 areas x 80 chrs)
Power	6 x AAA alkaline batteries (not supplied) AC adapter (Included (AD-24ES))

Items Included

Items included	PT-E100 labeller AC adapter 12mm Black on White Strong Adhesive laminated label cassette (8m long) User guide Carrying Case
----------------	--

Supplies

TZe Tapes	3.5, 6, 9, 12mm
-----------	-----------------

Built-in software

Built-in fonts	1 font
Built-in symbols	168
Character sizes	3 sizes
Character widths	3 widths: (extended, medium, condensed)
Font styles	9
Frames	1
Underline	Yes
Max. number of lines	2 lines
Horizontal alignment	Automatic length labels: left aligned Pre-set length labels: centre aligned
Pre-set format (auto format)	None
Tape length setting	Yes (30-300 mm)
Tape margin settings	Narrow, half, full, chain print
Tab function	Yes
Labelling functions	Cable wrap, cable flag
Automatic numbering	No
Mirror printing	No
Vertical printing	Yes
Copy (repeat) printing	Yes (1-9)
Print preview	Yes (graphic preview)
Auto power off	Yes
Unit change	Yes (inch/mm)
Language	20 languages (English, German, French, Spanish, Portuguese, Portuguese-Bra, Italian, Dutch, Danish, Norwegian, Swedish, Finish, Hungarian, Czech, Polish, Romanian, Slovene, Slovak, Croatian, Turkish)



Contact :



All specifications are correct at the time of printing. Brother is a registered trademark of Brother Industries Ltd.
Brand product names are registered trademarks or trademarks of respective companies

Brother Customer Service Centre: 152 Beach Road #01-01

Gateway East, Singapore 189721
Tel: 1800-BROTHER (1800-2768437)

Tel: 1800-BROTHER (1800-2768437)
Email: customerservice@brother.com.sg

Operating Hours: 9am - 7pm (Mon to
Closed on Sunday and Public Holidays)

For a list of authorised resellers, please log on to our website.



Label images shown are for illustrative purposes only and some aspects may not be reproducible on this model. Product specifications may be subject to change without notice.