

KCO

ABB contact for United  
Kingdom

### General Information

<b>Extended Product Type:</b>	KCO
<b>Product ID:</b>	1SNK900624R0000
<b>EAN:</b>	3472599006249
<b>Catalog Description:</b>	KCO Protecting Cover Kit - Dark Grey
<b>Long Description:</b>	KCO Protecting Cover Kit - Dark Grey

### Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Protecting Cover Kits

### Ordering

<b>EAN:</b>	3472599006249
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85369010

### Dimensions

<b>Product Net Height:</b>	74.4 mm
<b>Product Net Length:</b>	30.2 mm
<b>Product Net Depth:</b>	30.2 mm
<b>Product Net Weight:</b>	47.80 g

### Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	170 mm
<b>Package Level 1 Height:</b>	5 mm
<b>Package Level 1 Length:</b>	125 mm
<b>Package Level 1 Gross Weight:</b>	0.04780 kg
<b>Package Level 1 EAN:</b>	3472599006249
<b>Package Level 2 Units:</b>	100 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 2 Height:</b>	200 mm
<b>Package Level 2 Length:</b>	400 mm
<b>Package Level 3 Units:</b>	4800 piece
<b>Product Packing Type:</b>	Bag

### Environmental

<b>Ambient Air Temperature:</b>	Operation -55 +110 °C Storage -55 +110 °C
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	Compliant
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

### Technical UL/CSA

<b>Flammability According to UL94:</b>	V0
--	----

### Additional Information

<b>Ambient Temperature:</b>	-5 +40 °C
<b>Color:</b>	Dark Grey
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Function:</b>	Protecting Cover Kits
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Insulation Material:</b>	Polyamide

<b>Medium Description:</b>	Mount your protecting cover with the KCO versatile mounting kit (2 end stops, 2 sealing accessories): - Maintain the cover, - Reliably seal the access to the terminal assembly if needed, - Use it as well as an end stop.
<b>Mounting on DIN Rail:</b>	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Pollution Degree:</b>	3
<b>Product Main Type:</b>	KCO
<b>Product Name:</b>	Cover
<b>Recommended Screw Driver:</b>	4 mm
<b>RoHS Date:</b>	18 08 2005

---

### Certificates and Declarations (Document Number)

---

<b>GOST Certificate:</b>	1SND161005A1104
<b>RoHS Information:</b>	1SND230507F0202

---

### Classifications

---

<b>E-nummer:</b>	2925171
<b>Object Classification Code:</b>	X

---

