

D

D

C




C

B

B

A

A



- 注記:
- △ 相手ハウジングと所定の機能を満たしてかん合できること。
 - △ フードの反りは0.2以内。
 - 3 推奨取付けねじ: JIS B 1115 又は、1122 タッピンねじ
なべ1種、呼び径3を使用し締め付け後半田付けする。
(締め付けトルク: 0.4N・m 以下)
 - 4 適用製品規格: 108-5093
 - △ A 面より2mmの範囲で測定のこと。
 - 6 相手ハウジングとのかん合力は、29.4N以下
但し、リセプタクルコンタクトは含まない。

- NOTES:
- △ IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION
 - △ WARPAGE 0.2 MAX.
 - 3 RECOMMENDED MOUNTING SCREW; 3mmDIA, PAN HEAD, CLASS 1 TAPPING SCREW SPECIFIED IN JIS B1115, B1122 (TORQUE; 0.4N・m MAX.)
 - 4 SPEC. No. 108-5093
 - △ TO BE MEASURED WITHIN 2mm FROM A
 - 6 IN COUPLING WITH THE PLUG HOUSING MATING FORCE 29.4N MAX. WITHOUT REC CONTACTS.

SEE CUSTOMER DRAWING 6-172035-1			6-172035-1
SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	2-5172035-1
SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	1-5172035-1
PRE-TIN		NATURAL	5-172035-4
PRE-TIN		NATURAL	4-172035-1
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	GREEN 2-172035-4
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	NATURAL 2-172035-1
	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	GREEN 1-172035-4
	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	NATURAL 1-172035-1
	PRE-TIN		YELLOW 172035-7
OBSOLETE			GRAY 172035-6
OBSOLETE			BLUE 172035-5
OBSOLETE			GREEN 172035-4
		BROWN	172035-3
		BLACK	172035-2
PRE-TIN		NATURAL	172035-1
SOLDERING SIDE 半田付け部		CONTACT SIDE 接触部側	COLOR 色
CONTACT FINISH コンタクト仕上			PART NUMBER 製品型番

TOLERANCE UNLESS OTHERWISE SPECIFIED:
一般公差
0<X≤10 : ±0.2
10<X≤30 : ±0.25
30<X≤100 : ±0.3
ANGLE : ±3°
角度

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 31AUG07 CHK K.BETSUI 31AUG07 APVD K.BETSUI 31AUG07	Tyco Electronics Corporation Kawasaki, Japan	
DIMENSIONS: 単位: 特 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC 製品規格 APPLICATION SPEC 取付適用規格	NAME 氏名 9P VERTICAL TYPE CAP HOUSING ASS'Y MULTI-INTERLOCK CONN. (WIRE TO P.C.B.)	
MATERIAL 材料 HSG: 66 NYLON CONTACT: BRASS	FINISH 仕上 SEE TABLE	WEIGHT —	SIZE A2 CAGE CODE 00779 DRAWING NO. 172035	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 2:1 SHEET 1 of 1	REV F4