

**FEX FEX 3828 13 G**



Sample photo

**Order symbol:** FEX 3828 13 G  
**Product nbr:** 4130804  
**Description:** Enclosure, PC  
**Remarks:** EEx e II, EN 50014; IK 4J

**EAN:** 6418074008039  
**El. number:**  
 Finland: 3424663  
 Denmark: 8212026463  
 Italy: 7801150

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		378	278	130	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		14.9	10.9	5.1	Impact Resistance (EN 62262): IK 08/09
<b>Materials:</b>					Impact Resistance (EN 50014): 4J
<b>Material:</b>		Polycarbonate			Electrical insulation: Totally insulated
<b>Base colour:</b>		RAL 7035			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Cover colour:</b>		RAL 7035			UV resistance: UL 508
<b>Cover screws material:</b>		Polyamide			Flammability Rating (UL 746 C 5): UL 746C 5V
<b>Cover screws colour:</b>		Grey			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>		Silicone			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 120 °C			ATEX
<b>Continuous:</b>		-10 ... 80 °C			EC Certificate of Conformity
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		14 ... 175 °F			
<b>Accessories:</b>					
EKHVT		Mounting plate			
EKJVT		Mounting plate			
EKMVT		Mounting plate			
EKOVT		Mounting plate			
EKPVT		Mounting plate			
EKTVT		Mounting plate			
EKUVT		Mounting plate			
EKV 12		DIN-35 Mounting rail			
EKV 22		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			

