

TD44GT - Closed End

General Part Information	
Product Description	TD44GT
Article Number	82068.00
Rivet Type	i Closed End
Standard Bulk Pack Quantity	10000.00
Application / Features	i 



Geometry / Dimensions / Performance	
Head Style	i Domed
Body Diameter Ø (mm)	3.20
Body Length (mm)	8.00
Min. Grip Range (mm)	1.60
Max. Grip Range (mm)	3.20
Min. Hole Diameter (mm)	3.30
Max. Hole Diameter (mm)	3.40
Min. Flange Diameter (mm)	6.12
Max. Flange Diameter (mm)	6.65
Flange Thickness (mm)	0.87
Mandrel Diameter (mm)	2.00
Nominal Shear Strength (N)	2100.00
Nominal Tensile Strength (N)	2220.00

Material / Finish / Weight	
Body Material	i Stainless Steel
Mandrel Material	Stainless Steel
Finish	Clean
Weight per thousand (kg)	1.46