



ENGLISH

Datasheet

Stock No: 291-0038

# RS Pro ATEX M20 Brass Cable Gland



## Product Details

### Cable Glands M20

Brass body  
M20 thread  
To BS6207 pt2  
10 glands per box

### Approvals

Certificate: SIRA 02ATEX1305X

## Specifications:

Attribute	Value
Thread Size	M20
Material	Brass
Maximum Cable Diameter	6.2mm
Minimum Cable Diameter	5.2mm
Colour	Metallic
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+450°C
Standards Met	Sira 02ATEX1305X
Hazardous Area Certification	ATEX