



ENGLISH

Datasheet

## RS Pro Natural Nylon Screw Mount Cable Tie, 221.3mm x 4.2 mm

RS Stock No: **601-091**



### Product Details

RS Pro nylon 66 screw mount cable tie in natural colour, measures 221.3 x 4.2 mm. It comes with a screw mounting hole and is suitable for binding cable or components and securing them in position. The cable tie can be secured to panel with a single bolt.

### Features and Benefits

- Non-releasable
- Flammability rating UL94V-2
- Screw mount cable tie



ENGLISH

### Specifications:

Colour	Natural
Fire Behaviour	Flame Retardant
Length	221.3 mm
Material	Nylon 66
Maximum Bundle Diameter	52 mm
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Operating Temperature Range	-40 to +85°C
Product Name	Cable Tie
Quantity	100
Standards Met	UL 94 V-2, cURus, ABS, DNV, RoHS Compliant
Tensile Strength	215.6 N
Type	Screw Mount
Width	4.2 mm